

Sole and shaft cleaners

EDLW / EDSW / DZSW

When entering the unit, sensors activate the automatic rotation of the brushes and your soles and shafts are cleaned. The “walk-through” principle ensures time efficient cleaning, while your hygiene remains ideally ensured in the following area thanks to a combination of sole and shaft cleaning. If you only wish to clean shafts, the EDSW is the right unit. The installations have a low step height and are easy to use.

Options and/or accessories

Also available as a built-in model.



EDLW; sole and shaft cleaning

Your benefits

- Adjustable chemical dosing
- 4-year warranty on brushes
- Brushes can be removed without tools
- Automatic operation
- Hygienic construction and surface finish
- High user capacity



HACCP International certified products.



Various settings on these products can be adjusted.

Versions:

- ▶ EDLW
Sole and shaft cleaning
Article number: 83206000
- ▶ EDSW
Shaft cleaning
Article number: 83206005
- ▶ DZSW
Sole and shaft cleaning
Article number: 83202290

Other designs

and technical information



EDSW; shaft cleaning



DZSW, sole and shaft cleaning

Type	ELDW	EDSW	DZSW
Width / mm	939	890	890
Depth / mm	1286	1286	2225
Height / mm	1645 (from floor)	1835 (from floor)	1300 (from floor)
Height of step / mm	123	123	123
Safety	IP 65	IP 65	IP 65
Voltage / V	400	400	400
Number of phases	3	3	3
Frequency / Hz	50	50	50
Power / kW	0.75	0.75	1.2
Water connection in	3/4"	3/4"	3/4"
Water connection out	DN40	DN40	DN40
Weight / kg	180	160	265

Sole and shaft cleaners

EZW / ELZW / EZSW

By placing the sole of the shoe on the brush and holding the handle at the same time, your shoes are cleaned quickly and efficiently. The brushes activate via a sensor on the grip. The units are compact and therefore fit easily into smaller spaces.

Your benefits

- Adjustable chemical dosing
- 4-year warranty on brushes
- Brushes can be removed without tools
- Simple operation
- Hygienic construction and surface finish



HACCP International certified products.



The cleaning brushes are of excellent quality and have a standard 4-year warranty!



EZW, sole cleaning

Versions:

- ▶ EZW
Sole cleaner
Article number: 83206020
- ▶ ELZW
Sole and shaft cleaner
Article number: 83206010
- ▶ EZSW
Sole and shaft cleaner
Article number: 83206050

Other designs

and technical information



ELZW, sole and manual shaft cleaning



EZSW, sole and shaft cleaning

Type	EZW	ELZW	EZSW
Width / mm	507	507	603
Depth / mm	545	545	623
Height / mm	898	898	1062
Safety	IP 65	IP 65	IP 65
Voltage / V	230	230	400
Number of phases	1	1	3
Frequency / Hz	50	50	50
Power / kW	0.37	0.37	1
Water connection in	3/4"	3/4"	3/4"
Water connection out	DN40	DN40	DN40
Weight / kg	30	32	123

Sole and shoe side edge cleaner

EZR

When you place the sole of the shoe on the brush and hold the handle at the same time, your shoes are cleaned quickly and efficiently. The brushes activate via a button on the grip. Because the EZR also cleans the sides of your shoes, you can also be sure of maximum hygiene. The EZR is compact and fits in smaller spaces.

Your benefits

- Adjustable chemical dosing
- 4-year warranty on brushes
- Brushes can be removed without tools
- Simple operation
- Hygienic designed and surface finish



EZR, floor model



HACCP Internationally certified product.



The cleaning brushes are of excellent quality and have a standard 4-year warranty!

Versions:

- ▶ EZR floor model
Article number: 83206030
- ▶ EZR wall model
Article number: 83206040

Case study

and technical information



The EZR, floor model.

Type	EZR floor model	EZR wall model
Width / mm	697	697
Depth / mm	472	476
Height / mm	1186 (from floor)	1067
Voltage / V	400	400
Number of phases	3	3
Frequency / Hz	50	50
Power / kW	0.1	0.1
Water connection in	3/4"	3/4"
Water connection out	1 1/2"	1 1/2"
Weight / kg	70	68